

## Features

- Spray adjustable from a fine spray to a concentrated jet
- Tough
- Highly Efficient
- 24 Bar Maximum Working Pressure
- Threaded Connection 1/2" BSP Female

## RS PRO 1/2 in BSP Female Spray Gun, 24 bar

RS Stock No.: 175-6263



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

The RS PRO spray gun is a 1/2in BSP female spray gun. It has a water pattern that is adjustable from a fine spray to a concentrated jet. It has a sterling reputation, they're strong, reliable and diverse. The gun has been designed to work at a maximum temperature of 50°C. Working pressure of 24bar allows water applications in an industrial environment requiring a highly efficient wash down in facilities such:

- Food Processing Plants
- Pharmaceutical
- Chemical Processing
- Abattoirs
- Garages
- Factories

## General Specifications

Threaded Connection	1/2" BSP Female
Thread Size	1/2"
Thread Standard	BSP

## Mechanical Specifications

Maximum Working Pressure	24 Bar (350 psi)
Recommended Working Pressure	6-10 Bars
Minimum Working Pressure	NA
Maximum Operating Temperature	50 degrees°C
Capacity l/min	3L/min @ 5 Bar / 25 l/min@ 73 PSI 80L/min @ 24 Bar (350 psi)
Materials:	Rubber Parts: Silicone O-ring: Viton Inner Material: Brass
Dimensions	L 180mm H 150mm W 60mm
Net Weight	800g