

## Features

- Unique "snap on" locator design for full visibility of connector and wire insertion
- Parallel action for precision and consistent crimp results
- Full cycle crimp mechanism to ensure consistent, reliable crimp
- Ratchet release mechanism to clear miss-crimps and obstructions
- Precision eccentric adjustment for consistent performance and ability to calibrate
- Tool-less die closure adjustment for maintenance and calibration
- Small size makes it easy to use in confined areas
- Hole in handle allows attachment of safety strap
- Each tool has a unique serial number for traceability

## RS PRO RRB 0315 tool for crimping Super Seal type open barrel connectors 0.35 - 1.5 mm<sup>2</sup> with silicon seals

RS Stock No.: 810-0739



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

*Introducing the RS PRO ratchet-style crimp tool, specifically engineered for use with SuperSeal sealed connectors and uninsulated open barrel connectors within a wire size range of 0.35 to 1.5mm<sup>2</sup> (22-16 AWG), creating a precise 'B' type crimp profile.*

*This advanced tool features a parallel action and a full-cycle crimp mechanism, ensuring reliable and accurate crimping with every use. Equipped with a ratchet release mechanism and a tool-less die closure adjustment, maintenance and calibration are effortless.*

- Notably, this exceptional crimp tool boasts a unique "snap-on" locator design, providing users with clear visibility of both connector and wire insertion processes, enhancing precision and efficiency.*

## General Specifications

Weight	317 gr/0.7 lb
Wire size	0.35-1.5 mm <sup>2</sup> / AWG 22-AWG 16
Crimp dimensions mm/mm <sup>2</sup>	0,35 - 0,5/0,75 - 1,5
Crimp dimensions inch/AWG	AWG 22 - AWG 20/AWG 20 - AWG 16
Connector	Connectors with seal, 1.5 system type. Description
Life span, cycles	50,000

## Mechanical Specifications

Length	190 mm/7.48"
Width	21 mm/0.83"
Height	74 mm/2.91"