






SPECIFICATIONS (规格)

- Voltage Rating (额定电压): 600V AC, DC
- Current Rating (额定电流): 7A, AC, DC
- Withstanding Voltage (耐电压): 1500V AC/minute
- Insulation Resistance (绝缘电阻): 1000MΩ min
- Temperature Range (工作温度): -25° C ~ +85° C
- Contact Resistance (接触电阻): 10mΩ max
- Material:
- Insulator: Nylon 66 UL94V-2 or UL94V-0



Poles	PART NO.	Dimension mm	
		A	B
2*1	2-5557H02P-BM00	-	5.40
2*2	2-5557H04P-BM00	4.20	9.60
2*3	2-5557H06P-BM00	8.40	13.80
2*4	2-5557H08P-BM00	12.60	18.00
2*5	2-5557H10P-BM00	16.80	22.20
2*6	2-5557H12P-BM00	21.00	26.40
2*7	2-5557H14P-BM00	25.20	30.60
2*8	2-5557H16P-BM00	29.40	34.80
2*9	2-5557H18P-BM00	33.60	39.00
2*10	2-5557H20P-BM00	37.80	43.20
2*11	2-5557H22P-BM00	42.00	47.40
2*12	2-5557H24P-BM00	46.20	51.60



TOLERANCE TABLE	
.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRY CO., LTD				
CHECKED:	DATE:	TITLE: 5557HP-2*XP 公壳 (MX4.2)				
DRAWN: SX	DATE: 2024-06-18	PART. P/N	2-5557HXXP-BM00			
		UNIT	mm	SCALE	free	
		FILE NO.	Ckmtw-5557-0007	REV.	A	DGHW