

Features

- Setscrews are fully threaded and designed to connect two or more objects
- Example applications include automotive, machinery, engines, manufacturing, industrial equipment, white goods
- The hexagon head enables the setscrew to be tightened and loosened, driven by a socket drive or spanner
- Setscrews can be removed and reinserted endless times - ideal for maintenance and repair projects
- Manufactured from A2 stainless steel, they are ideal for external - as well as internal use, offering fantastic resistance against corrosion
- Comply with DIN 933 specifications

RS PRO Hex Bolts

RS Stock No.: see list



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- *Advance your fastening game with this superb RS PRO hex bolt. Our innovative, fully threaded marvel will simplify your project assemblies. No more messing with nuts – it screws direct into a tapped hole, and you're good to go. Typically used in automotive to industrial equipment, the RS PRO hex bolt is the ultimate problem-solver.*
- *The versatile hexagon head makes tightening and loosening a breeze, whether using a socket drive or spanner. The advantage of this bolt is the A2/304 stainless steel construction, and you can remove and reinsert repeatedly without the risk of damaging the threads for unparalleled flexibility on the job.*

General Specifications

d1	M3	M4	M5	M6	M8	M10	M12	M14	M16	M20
e	6.01	7.66	8.79	11.05	14.38	18.9	21.1	24.49	26.75	33.53
k	2	2.8	3.5	4	5.3	6.4	7.5	8.8	10	12.5
s	5.5	7	8	10	13	17	19	22	24	30

Similar Products

RS Stock No.	Size	RS Stock No.	Size
2873865	M3 X 6	520289	M10 X 30
2873866	M3 X 8	520273	M10 X 35
2874035	M3 X 10	520295	M10 X 40
2873864	M3 X 12	7976339	M10 X 45
2873865	M3 X 16	520302	M10 X 50
2873866	M3 X 20	2873935	M10 X 55
2873867	M3 X 25	276588	M10 X 60
2873868	M3 X 30	2873936	M10 X 65
2873915	M4 X 8	276594	M10 X 70
520009	M4 X 10	2873937	M10 X 75
520015	M4 X 12	2873938	M10 X 80
520021	M4 X 16	2873940	M10 X 100
520037	M4 X 20	2874039	M10 X 120
520043	M4 X 25	2874018	M10 X 130

Hex Bolts



2873916	M4 X 30	2874019	M10 X 140
2873918	M4 X 40	2874040	M10 X 150
2873919	M4 X 50	520318	M12 X 20
2873920	M5 X 8	520324	M12 X 25
2873921	M5 X 10	520330	M12 X 30
520065	M5 X 12	7976333	M12 X 35
520071	M5 X 16	520346	M12 X 40
520087	M5 X 20	7976342	M12 X 45
520093	M5 X 25	520352	M12 X 50
520100	M5 X 30	7976345	M12 X 55
2873922	M5 X 35	520368	M12 X 60
289001	M5 X 40	276601	M12 X 70
2874017	M5 X 45	276617	M12 X 80
2873923	M5 X 50	2873941	M12 X 90
520116	M6 X 10	2873942	M12 X 100
7976305	M6 X 12	2874041	M12 X 110
520122	M6 X 16	2874042	M12 X 120
520138	M6 X 20	2874043	M12 X 130
520150	M6 X 30	2873882	M12 X 140
7976314	M6 X 35	2874044	M12 X 150
520166	M6 X 40	2874045	M16 X 20
2873924	M6 X 45	2873943	M16 X 25
520172	M6 X 50	2873944	M16 X 30
2873925	M6 X 55	2873946	M16 X 35
289017	M6 X 60	2873947	M16 X 40
2874036	M6 X 65	276651	M16 X 45
289023	M6 X 70	276667	M16 X 50
2873926	M6 X 75	2873948	M16 X 55
2873927	M6 X 80	276673	M16 X 60
2873928	M6 X 90	2873949	M16 X 65
2873929	M6 X 100	276689	M16 X 70
7976317	M8 X 10	2873950	M16 X 75
820188	M8 X 12	276695	M16 X 80
520194	M8 X 16	2873952	M16 X 90
520201	M8 X 20	2873953	M16 X 100
520217	M8 X 25	2874046	M16 X 120

520223	M8 X 30	2874020	M16 X 130
79763113	M8 X 35	2874047	M16 X 150
520239	M8 X 40	2874048	M20 X 30
7976320	M8 X 45	276702	M20 X 40
520245	M8 X 50	2873954	M20 X 45
7996323	M8 X 55	276718	M20 X 50
289039	M8 X 60	2873955	M20 X 55
289045	M8 X 70	2873956	M20 X 60
2873930	M8 X 75	2874050	M20 X 65
2873931	M8 X 80	276730	M20 X 70
2873932	M8 X 90	2873957	M20 X 75
2873933	M8 X 100	276746	M20 X 80
2874037	M8 X 120	2873958	M20 X 90
2873871	M8 X 130	276752	M20 X 100
2874038	M8 X 150	2874021	M20 X 110
2873934	M10 X 12	2874051	M20 X 120
520251	M10 X 16	2874022	M20 X 130
520267	M10 X 20	2874052	M20 X 140
520273	M10 X 25	2874053	M20 X 150

