

Features

- For the electronic industry, watch-makers, jewellers and laboratory and medical device manufacturing applications in moderately aggressive chemical environments
- Nonmagnetisable
- Corrosion resistance to most chemicals, salts and acids
- Generally used where corrosion resistance and toughness are primary requirements
- Various lengths and point types available

RS PRO Tweezers

RS Stock No.: 1369712



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Type 65A high precision tweezers are suitable to delicate applications which require holding a small component firmly while granting maximum visibility. The bent geometry provides maximum visibility and increased ergonomics.

General Specifications

Category	Premium Economy tweezers
Model Number	65A.SA.6
Country of origin	Italy
Tip Style	65A
Tip Type	bent, very fine, very sharp

Electrical Specifications

ESD Safe	No
----------	----

Mechanical Specifications

Overall Length	140.0 (mm)
Anti-Acid	Yes
Anti-Magnetic	Yes
Material	Anti-Acid/Anti-Magnetic Stainless Steel
Full Body coating/finishing	Sandblasted
Product Height	11.0 (mm)
Product Width	9.0 (mm)
Degree of Bending	30.0°
Tip Thickness	0.09 (mm)
Tip Width	0.12 (mm)
Weight	13.0 (g)