

FEATURES

- Galvanised, Stainless Steel or Plastic Options
- Many Grades
- Easy to Install
- Use CRG Fixing Plate

RS PRO Cansorb Galv 145x600mm Carbon 1.1kg

RS Stock No.: 2550980



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Cansorb refillable carbon cylinders are a versatile and simple filter for use in most odour and fume reduction applications.

General Specifications

Filter Size Actual Diameter x Length (mm)	145 x 600 mm
Application	General Odour Removal
Rated Capacity	75 m ³ /hr
Initial Pressure Drop	65 Pa
Final Pressure Drop*	165 Pa
*Final Recommended Pressure Drop to EN13053:2019	
Maximum Operating Temperature 80C	