

Features

- Excellent electrical conduction
- Very low contact resistance
- Robust contact point pressure when connected
- High durability for a high number of mating cycles

RS PRO Binding Posts

RS Stock No.: 423-201



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- *Black insulated terminal binding post with a 4mm socket. Panel insulating bushes have a location keyway, maximum panel thickness 12.7mm. Threaded termination supplied with solder tag washer. Thread size 4BA (3.6mm or 0.141inch).*
- *High-quality moulded parts in acetal*
- *Contact material Nickel plated brass*
- *Accepts standard 4mm plug in top*
- *Height above panel: 24mm to 32mm*
- *Overall dia. 14mm*

General Specifications

Colour:	Black
Contact:	Material Brass
Contact Plating:	Nickel
Gender:	Female
Insulation Material:	POM
Termination Method:	Solder

Mechanical Specifications

Length:	52.9mm
---------	--------

Electrical Specifications

Current Rating:	16A
Voltage Rating:	50V

Dimensions

