

FEATURES

- The nickel plated body provides heavy duty structural quality
- 50 Ω impedance
- Operating frequency is 4GHz

RS PRO Family Name

RS Stock No.: 2469453



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These coaxial adapters are designed to provide an efficient means of connecting coaxial cable assemblies through panel mounting connections.

These connectors are made from industry-standard components and are most commonly used to connect radio and television broadcasting equipment.

Coaxial adapters are available for a variety of radio frequency (RF) signal applications as well as medical and test equipment.

General Specifications

Adapter Type	BNC Plug to BNC Plug
Adapter Type A	BNC
Adapter Type B	BNC
Gender A	Male
Gender B	Male
Body Orientation	Straight
Contact Plating	Nickel
Body Plating	Nickel 100u"
Body Material	Brass

Electrical Specifications

Temperature Range	-65° ~ +165°
Characteristic Impedance	50Ω
Frequency Range	0~4GHz
Working Voltage	500V
Insulation Resistance	≥1000MΩ
Medium Pressure	500V(rms)
VSWR	≤1.3
Working Life	500Cycles

Protection Category

--	--

Additional Information

EAN	
Custom Tariff Number	

Classification

eCl@ss (Version)	
UNSPSC (Version)	

Approvals

Declarations	CE
Hazardous Area Certification	
Standards Met	ROHS

Similar Products

Stock No.	Brand	Product Name	Attribute 1	Attribute 2	Attribute 3
5464544	RS PRO	Radio frequency adapter	50Ω impedance	Operating frequency is 4GHz	

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories

