

Features

- Levelling Feet
- Height Adjustable
- Black polyamide material
- Mild Steel thread
- Thread size: M8 or M10
- Load capacity: 500 kg, 600 kg

RS PRO Adjustable Feet

RS Stock No.: 1854497,1854499,
1854500 ,1854501



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- The RS Pro Height Adjustable mounts are used for levelling and support in many applications including food processing units, packing systems and conveyor systems.
- The Plastic Foot is made from a black polyamide material, reinforced by fiber glass along with a Mild Steel thread makes this an economical solution for your levelling needs.

General Specifications

Item Code	Description	A (mm)	B (mm)	D (mm)	F (mm)	H (mm)	H1 (mm)	Static Load (kg)
1854497	Mild Steel Threaded Mount with Plastic Foot	16	50	40	M8	66	69	500
1854499	Mild Steel Threaded Mount with Plastic Foot	20	50	50	M8	70	73	600
1854500	Mild Steel Threaded Mount with Plastic Foot	16	50	40	M10	66	69	500
1854501	Mild Steel Threaded Mount with Plastic Foot	20	50	50	M10	70	73	600

