

Features

- Loop powered model
- Compact model size
- Wire sealable terminal covers
- 21mm Aperture Hole
- 4/20mA DC (15-30V DC loop-powered 24V nominal, maximum load 600ohms@24VDC)

RS PRO Current Transformer

RS Stock No.: 180-441



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

A Loop powered compact current transformer intended for based mounting with a 21mm aperture hole.

General Specification

Current Ratio	10A/4-20mA
Bore Size	21mm
Transformer Type	Base Mounted
Supply Voltage	24V DC
Input Current	10A
Output Current	4-20mA
Overall Height	65mm
Overall Width	44mm
Overall Depth	30mm
Minimum Temperature	-5°C
Maximum Temperature	55°C
Mounting Type	Foot
Applications	Instrumentation for Switchgear and control panels

