

特点

- 超值 esd 工作台垫
- 静电耗散层
- 导电层
- 所有工作台垫均配有 10 mm 螺柱角

灰色工作台 / 地板 esd 安全垫、 1.2m x 600mm x 3.2mm RS 号:

466-1659



RS 认证产品为您提供所有产品类别的专业品质部件。我们的产品系列经过工程师测试、提供与领先品牌相当的质量、而无需支付高昂的价格。

商品描述属性

RS PRO ESD 保护垫简介。这些保护垫旨在防止静电放电对 ESD 敏感物品和组件造成损坏。使用时，垫子会释放静电，将物品接地并保护表面免受磨损。

提供选件

- RS 号: [466-1643](#). - 600 x 1200 mm - 蓝色
- RS 号: [466-1665](#). - 1200 x 1800 mm - 蓝色
- RS 号: [466-1659](#). - 600 x 1200 mm - 灰色
- RS 号: [466-1671](#). - 1200 x 1800 毫米 - 灰色

一般规格

使用类型	工作台、地板
适用于	耐化学性, 连续监控, 焊接
颜色	灰色
符合 en 61340-5-1	是的
曲面纹理类型	平滑
材料	抗静电 (导电) 和静电耗散材料、带合成橡胶
材料层数	3
应用	esd 实验室, 处理 esd 敏感设备, 抗静电实验室, esd 洁净室 非常适合维修台式机、笔记本电脑、移动设备和所有其他电子设备、工作台

电气规格

表面电阻	$1 \times 10^6 \leq r \leq 1 \times 10^9 \Omega$
底部电阻	$1 \times 10^3 \leq r \leq 1 \times 10^6 \Omega$
容积电阻	$1 \times 10^5 \leq r \leq 1 \times 10^8 \Omega$
耐温	180 (瞬时温度) °C

机械规格

尺寸	1.2m x 0.6m
长度	1.2m
宽度	600mm
厚度	3.2mm

操作环境规格

温度	20-26. °c.
相对湿度	40-65%

ARTICLE:	DESCRIPTION:	SIZE:	ADDITIONAL NOTES:
466-1643	ESD Bench Matting – 3 Layer, Smooth Finish	600 x 1200mm	Blue
466-1665	ESD Bench Matting – 3 Layer, Smooth Finish	1200 x 1800mm	Blue
466-1659	ESD Bench Matting – 3 Layer, Smooth Finish	600 x 1200mm	Grey
466-1671	ESD Bench Matting – 3 Layer, Smooth Finish	1200 x 1800mm	Grey
287-7587	ESD Bench Matting – 2 Layer, Smooth Finish	600 x 1200mm	Beige
327-3122	ESD Bench Matting – 2 Layer, Smooth Finish	600 x 1200mm	Green
287-7593	ESD Bench Matting – 2 Layer, Smooth Finish	600 x 1200mm	Grey