

FEATURES

- Durable polycarbonate design in smoke grey for 2, 6, 8 and 12 modules
- Available with or without break break-away finger protection panel
- IP67 rating offering protection from dust and liquids (Stock no. 297-1184 features an IP44 rating and is not waterproof)
- Ideal for troubleshooting and accessing enclosures without opening them
- Can be used indoors and outdoors
- Wide operating temperature range of -25°C to +80°C
- Spring loaded mechanism that can be secured with thumb screws

RS PRO Enclosure Accessories - 127 x 47 x 93.5mm Inspection Window

RS Stock No.: 2971235



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Inspection Windows for Enclosures

Introducing inspection windows for enclosures from our trusted and reliable own brand RS PRO. This range of inspection windows are an excellent addition of accessories for enclosures, increasing visibility of internal electrical parts and components without coming into contact with them or opening the lid of the enclosure. This range of spring loaded inspection windows are ideal for troubleshooting on the go and can be secured via thumb screws for extra security. These inspection windows for enclosures are made using a durable polycarbonate and offer an IP rating of IP67, offering excellent protection from dust and liquids indoors and outdoors.

General Specifications

Type	Inspection Window
For Use With	DIN 43880, 46277-3
Colour	Grey
Application	Multi-purpose

Mechanical Specifications

Material	Polycarbonate
Dimension	127 x 47 x 93.5mm
Length	127mm
Width	47mm
Height	94mm

Protection Category

IP Rating	IP67
-----------	------

Approvals

Declarations	RoHS Certificate of Compliance
--------------	--------------------------------

Similar Products

Stock No.	Brand	Product Name	Type	Colour	For Use With
2971184	RS PRO	49 x 27 x 78mm Inspection Window	Inspection Window	Grey	for use with 46277-3, DIN 43880
2971207	RS PRO	127 x 24 x 93.5mm Inspection Window	Inspection Window	Grey	for use with 46277-3, DIN 43880

Diagrams / Illustrations / Installation Diagrams

