

FEATURES

- The nickel plated body provides heavy duty structural quality
- 50 Ω impedance
- Operating frequency is 4GHz
- Gold contacts ensure maximum efficiency

RS PRO Family Name

RS Stock No.: 2469456



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

50 Ω BNC series crimp jack with waterproof IP68 internal seal prevents gas and moisture from entering between insulators, between internal and external conductors, and between connector body and panel mounting holes. This waterproof BNC series jack features a nickel-plated brass body, teflon insulation, rubber 'O' rings, silicone gaskets and gold-plated centre contacts. The appropriate RF coaxial cable for this IP68 seal BNC series jack is RG174/U

General Specifications

Type of connector	BNC connector
Body Plating	Nickel
Contact Material	Brass
Pin Plating	Gold
Bulkhead	Yes
Cable Type	RG174/U
Gender	Female

Electrical Specifications

Temperature Range	-45° ~ +165°
Characteristic Impedance	50 Ω
Frequency Range	0~4GHz
Working Voltage	335V
Insulation Resistance	$\geq 1000M\Omega$
Medium Pressure	750V(rms)
Working Life	500Cycles

Protection Category

--	--

Additional Information

EAN	
Custom Tariff Number	

Classification

eCl@ss (Version)	
UNSPSC (Version)	

Approvals

Declarations	CE
Hazardous Area Certification	
Standards Met	ROHS

Similar Products

Stock No.	Brand	Product Name	Attribute 1	Attribute 2	Attribute 3
7933594	RS PRO	RF adapter	50Ω impedance	Operating frequency is 4GHz	

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories

