

Remark:

1.MATERIAL:

- 1.1 Housing:thermoplastic plastics.
- 1.2 terminals:Copper Alloy
- 1.3 Shell:Copper Alloy/SPCC.

2.characteristics:


- 2.1 Rating Voltage : 30V AC.
- 2.2 Rating Current:PIN1&PIN4(Vbus&Correponding ground PIN)
1.8A MAX Other PINS 0.25A min.
- 2.3 Contact Resistance:PIN1&PIN4:30 mΩ MAX. Other PINS: 50 mΩ
- 2.4 Insulation Resistance:100 MΩ MIN.
- 2.5 Withstanding Voltage:AC 100V between adjacent contacts
- 2.6 Mating force: 3.57Kgf MAX(35N MAX)
- 2.7 Extraction force:1Kgf Min(9.8N Min)
- 2.8 Life test:1500Cycles MIN.
- 2.9 Temperature Range: -40℃~+85℃.

Pin Number	Signal Name	Pin Number	Signal Name
1	VBUS	5	StdA_SSRX-
2	D-	6	StdA_SSRX+
3	D+	7	GND_DRAIN
4	GND	8	StdA_SSTX-
Shell	Shield	9	StdA_SSTX+

GENERAL TOLERANCE	DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD	
DIM. .x ±0.30 .xx ±0.20 .xxx ±0.10	TITLE: Type-A 母弯插 USB3.0 蓝色	
GENERAL ANGLE: .x° ±3.0° .xx° ±2.0° .xxx°	DWG. NO.: USB3.0-L16.8	CHECKED: MAX
	PART NO.: USB3.0-L16.8	DRAWN: ELLA
UNIT: mm	SCALE: none	SHEET: 1 of 1
	DWG. SIZE: A4	LAYER: bxconn
		APPROVED: WILL

BXCONN[®]





REV.	DESCRIPTION	ECN NO.	NAME	DATE

每盒100PCS.

备注:

1. 将全检后的良品如图示摆入PVC透明吸塑盒中, 每盒包装100PCS, 摆好后, 盖好上盖
2. 将装好产品的吸塑盒每箱放两排, 每排放两捆。放入规格为490*310*315mm的纸箱中, 每箱装5000PCS.
3. 用透明胶工字型封箱, 用美纹胶纸贴上我司产品标签, 出货前需更换为业务提供的客户标签. PASS章盖于我司产品标签上.

共25层
50盒

25盒分两层放入纸箱中, 上层10盒/捆, 下层15盒/捆
每箱内放两排50盒, 共5000PCS产品.

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				 
DIM.	TOL.	TITLE: Type-A 母弯插 USB3.0 蓝色				
.x	±0.30	DWG. NO.: USB3.0-L16.8		CHECKED: MAX		
.xx	±0.20	PART NO.: USB3.0-L16.8		DRAWN: ELLA		
.xxx	±0.10	UNIT: mm		SCALE: none	SHEET: 1 of 1	
GENERAL ANGLE:		DWG. SIZE: A4		LAYER: bxconn		
.x°	±3.0°	APPROVED: WILL				
.xx°	±2.0°					
.xxx°						