





A		B		C		D		E	
REV.	DESCRIPTION				ECN NO.	NAME	DATE		

NOTES:

- 1.BASE: PA66
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 1.25
- 2.Voltage Rating: 125V AC DC
- 3.Current Rating: 1A AC DC
- 4.Insulation Resistance: 100MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃



Part No	Pin	A	B	C	D
WF-MX1.25-2PWZ	2	1.25	4.40	3.20	
WF-MX1.25-3PWZ	3	2.50	5.65	4.45	
WF-MX1.25-4PWZ	4	3.75	6.90	5.70	2.50
WF-MX1.25-5PWZ	5	5.00	8.15	6.95	3.75
WF-MX1.25-6PWZ	6	6.25	9.40	8.20	5.00
WF-MX1.25-7PWZ	7	7.50	10.65	9.45	6.25
WF-MX1.25-8PWZ	8	8.75	11.90	10.70	7.50
WF-MX1.25-9PWZ	9	10.00	13.15	11.95	8.75
WF-MX1.25-10PWZ	10	11.25	14.40	13.20	10.00
WF-MX1.25-11PWZ	11	12.50	15.65	14.45	11.25
WF-MX1.25-12PWZ	12	13.75	16.90	15.70	12.50
WF-MX1.25-13PWZ	13	15.00	18.15	16.95	13.75
WF-MX1.25-14PWZ	14	16.25	19.40	18.20	15.00
WF-MX1.25-15PWZ	15	17.50	20.65	19.45	16.25
WF-MX1.25-16PWZ	16	18.75	21.90	20.70	17.50

GENERAL TOLERANCE	DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD			
DIM. .x ±0.20 .xx ±0.10 .xxx ±0.05	TITLE: WAFER 1.25 弯针			
GENERAL ANGLE: .x' ±5.0° .xx' ±3.0° .xxx'	DWG. NO.: WF-MX1.25-XPWZ		CHECKED: MAX	
	PART NO.: WF-MX1.25-XPWZ		DRAWN: ELLA	
	UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4
			LAYER: bxconn	APPROVED: WILL

BXCONN®

