

FEATURES

- 18W Axial Fan
- Airflow 2.33 m³/m
- Ball Bearings
50,000Hrs (40°C)
- Operating
Temperature -10°C -
+70°C

RS PRO Axial Fans

RS Stock No.: 2557321



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS Pro range of AC axial fans are the ideal solution for a wide range of cooling applications such as network communications and information technology equipment. Reliability and long life are assured with a ball bearing life of 50,000Hrs (at 40°C) and operating temperatures of -10°C up to +65°C. These products have been tested by engineers and have passed as RS Professionally Approved Products for quality and peace of mind.

General Specifications

Fan Type	AC Axial Fan
Frame Material	Aluminium Alloy
Frame Colour	Black
Rated Voltage	230VAC
Hz	50
Rated Current (A)	0.12
Input Power	18W
Speed (RPM)	2600
Max Air Volume (m³/m)	2.33

Mechanical Specifications

Length	120mm
Width	120mm
Thickness	38mm
Mounting Hole Diameter	4.4mm

Approvals

Compliance/Certifications	CE, UKCA, RoHS
----------------------------------	----------------

Similar Products

Parameters	2557319	2557320	2557322	2557323
Brand	RS PRO	RS PRO	RS PRO	RS PRO
Fan Type	AC Axial Fan	AC Axial Fan	AC Axial Fan	AC Axial Fan
Frame Material	Plastic	Plastic	Plastic	Plastic
Frame Colour	Black	Black	Black	Black
Rated Voltage	115VAC	115VAC	230VAC	230VAC
Hz	50	50	50	50
Rated Current (A)	0.24	0.24	0.12	0.12
Input Power	18W	20W	19W	19W
Speed (RPM)	2600	2600	2600	2600
Max Air Volume (m³/m)	2.3	2.3	2.33	2.33
Length	120mm	120mm	120mm	120mm
Width	120mm	120mm	120mm	120mm
Thickness	38mm	38mm	38mm	38mm
Mounting Hole Diameter	4.4mm	4.4mm	4.4mm	4.4mm
Compliance/Certifications	CE, UKCA, RoHS	CE, UKCA, RoHS	CE, UKCA, RoHS	CE, UKCA, RoHS

Parameters	2557324	2557325
Brand	RS PRO	RS PRO
Fan Type	AC Axial Fan	AC Axial Fan
Frame Material	Plastic	Plastic
Frame Colour	Black	Black
Rated Voltage	230VAC	230VAC
Hz	50	50
Rated Current (A)	0.08	0.1
Input Power	13W	16W
Speed (RPM)	2250	2500
Max Air Volume (m³/m)	1.83	2.11
Length	120mm	120mm
Width	120mm	120mm
Thickness	38mm	38mm
Mounting Hole Diameter	4.4mm	4.4mm
Compliance/Certifications	CE, UKCA, RoHS	CE, UKCA, RoHS

