

FEATURES

- 50 Ω impedance
- Operating frequency is 1GHz
- BNC plug to BNC 2 x socket RF adapter
- Nickel plated body and gold plated centre contact

RS PRO BNC dual socket to plug

RS Stock No.: 2177793



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

BNC plug to BNC 2 x socket RF adapter features bayonet couplings, nickel plated body and gold plated centre contact. It has 50Ω impedance. This adapter is suitable for a variety of applications including video signalling and test equipment.

Suitable for a variety of applications including video signalling and test equipment.

General Specifications

Type of coaxial connector	BNC dual socket to plug
Body Plating	Nickel
Termination method	Cable
Contact Material	Brass
Contact Plating	Nickel
Gender A	Plug
Gender B	Socket
Mounting type	Panel mount

Electrical Specifications

Temperature Range	-65° ~ +165°
Characteristic Impedance	50Ω
Frequency Range	0~4GHz
Working Voltage	500V
Insulation Resistance	≥1000MΩ
Medium Pressure	1000V(rms)
VSWR	≤1.3
Working Life	500Cycles

Approvals

Declarations	CE
Hazardous Area Certification	
Standards Met	ROHS

Similar Products

Stock No.	Brand	Product Name	Attribute 1	Attribute 2	Attribute 3
3034961	RS PRO	BNC dual socket to plug	50Ω impedance	Operating frequency is 4GHz	

