

A	B	C	D	E
---	---	---	---	---

REV.	DESCRIPTION	ECN NO.	NAME	DATE

NOTES:

MATERIAL

- 1.HOUSING MATERIAL: GLASS FILLED POLYESTER UL94V-0.
- 2.CONTACT MATERIAL: PHOSPHOR BRONZE $\phi 0.46\text{mm}$.
- 3.PLATING: GOLD FLASH PLATING OVER NICKEL.
- 4.SHIELD: BRASS T0.20mm 40u" NICKEL PLATED.

ELECTRICAL



- 1.VOLTAGE RATING: 125 VAC RMS.
- 2.CURRENT RATING: 1.5 AMP.
- 3.CONTACT RESISTANCE: 40 MILLIOHMS MAX.
- 4.INSULATION RESISTANCE: 500 MEGOHMS MIN @ 100V DC .
- 5.DIELECTRIC DIELECTRIC RESISTANCE: 500V DC RMS 50Hz. 1MIN.

MECHANICAL




- 1.DURRABILITY: 750 CYCLES MIN.
- 2.MATING/UNMATING FORCE: 2.24 KG.F MAX.

ENVIRONMENTAL:

- 1.STORAGE: $-40^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
- 2.OPERATION: $-40^{\circ}\text{C}\sim+85^{\circ}\text{C}$.



8	—
7	—
6	RX-
5	—
4	—
3	RX+
2	TX-
1	TX+
PIN	说明



PCBLAYOUT
TOL:±0.05

焊脚尺寸以顺畅过孔规为准

GENERAL TOLERANCE	DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD		
DIM. TOL.	TITLE: RJ45 B型无弹 带灯 左黄右绿 DIP		
.x ±0.35	DWG. NO.: RJ45-R-8-0	CHECKED: MAX	
.xx ±0.25	PART NO.: RJ45-R-8-0	DRAWN: ELLA	
.xxx ±0.15	UNIT: mm	SCALE: none	
GENERAL ANGLE:	SHEET: 1 of 1	DWG. SIZE: A4	APPROVED: WILL
x.° ±3.0°	LAYER: bxcn		
x.x° ±2.0°			
x.xx° ±1.0°			