

特点

- 可将探头牢固连接到热电偶套管或隔板
- 可快速轻松地调整传感器浸入长度
- 耐压力应用
- **BSPP** 平行螺纹
- **303** 不锈钢，具有耐用性和耐腐蚀性

RS Pro 热电偶压缩配件，适合与具有 3mm 探头直径，1/8 BSPP 的热电偶一起使用

RS 库存号： 381-7340



RS 认证产品为您提供所有产品类别的专业品质部件。我们的产品系列经过工程师测试、提供与杰出品牌相当的质量、而无需支付高昂的价格。

商品描述属性 1

RS Pro 的高质量 303 不锈钢压缩配件或压缩固定头用于将热电偶或 RTD (电阻温度探测器) 的探头牢固地连接到工艺配件，如法兰板和热电偶套管。此不锈钢压缩配件还提供了一种快速方便的方法，可将探头固定在测量过程中的正确浸入深度。

附件

提供用于这些压缩配件的锁紧螺母

库存号 [762-1171](#) 是用于 BSPP 1/8 配件的锁紧螺母

库存号 [762-1174](#) 是用于 BSPP 1/4 配件的锁紧螺母

库存号 [762-1178](#) 是用于 BSPP 1/2 配件的锁紧螺母

一般规格

附件类型	热电偶压缩配件
适合与一起使用	热电偶
应用	1/8 BSPP 连接器

机械规格

连接器尺寸	1/8"
连接器类型	BSP 平行
至合适	1.0 mm
探头直径	1.0 mm

认证

合规性 / 认证	rohs
----------	------



(BSP, BSPT, M8, M16 & M20)



(BSP parallel example - 381-7362, see below for other sizes)



(BSPT tapered example – 286-787, see below for other sizes)



BSP Parallel:

Type	Thread Size	Thread Type	Suits Probe Ø	Allied code	RS order code
St/Steel	1/8"	BSP Parallel	1.0mm	70654828	804-7975
St/Steel	1/8"	BSP Parallel	1.5mm	70643728	381-7334
St/Steel	1/8"	BSP Parallel	2.0mm		131-4765
St/Steel	1/8"	BSP Parallel	3.0mm	70643729	381-7340
St/Steel	1/8"	BSP Parallel	4.0mm	70657784	839-9566
St/Steel	1/8"	BSP Parallel	4.5mm	70657785	839-9569
St/Steel	1/8"	BSP Parallel	6.0mm	70643730	381-7356
St/Steel	1/8"	BSP Parallel	1/4"		110-4476
St/Steel	1/8"	BSP Parallel	1/8"	70657782	839-9557
St/Steel	1/8"	BSP Parallel	3/16"	70657783	839-9563
St/Steel	1/4"	BSP Parallel	1.5mm		178-0960
St/Steel	1/4"	BSP Parallel	3.0mm	70643731	381-7362
St/Steel	1/4"	BSP Parallel	4.0mm		178-0961
St/Steel	1/4"	BSP Parallel	4.5mm	70657786	839-9572
St/Steel	1/4"	BSP Parallel	6.0mm	70643732	381-7378
St/Steel	1/4"	BSP Parallel	1/4"	70657787	839-9575
St/Steel	1/4"	BSP Parallel	1/8"		178-0962
St/Steel	1/4"	BSP Parallel	3/16"	70657779	839-9547
St/Steel	1/2"	BSP Parallel	3.0mm	70657788	839-9579
St/Steel	1/2"	BSP Parallel	4.5mm	70657791	839-9588
St/Steel	1/2"	BSP Parallel	6.0mm	70643735	381-7407
St/Steel	1/2"	BSP Parallel	8.0mm	70657789	839-9581

BSPT Tapered:

Type	Thread Size	Thread Type	Suits Probe Ø	Allied code	RS order code
St/Steel	1/8"	BSPT Tapered	1.0mm	70654831	804-7984
St/Steel	1/8"	BSPT Tapered	1.5mm	70637825	286-743
St/Steel	1/8"	BSPT Tapered	2.0mm		131-4766
St/Steel	1/8"	BSPT Tapered	3.0mm	70636461	158-610
St/Steel	1/8"	BSPT Tapered	4.0mm		178-0963
St/Steel	1/8"	BSPT Tapered	4.5mm	70637826	286-759
St/Steel	1/8"	BSPT Tapered	6.0mm	70657792	839-9591
St/Steel	1/8"	BSPT Tapered	1/4"		110-4475
St/Steel	1/8"	BSPT Tapered	1/8"	70657793	839-9594
St/Steel	1/8"	BSPT Tapered	3/16"	70657794	839-9597
St/Steel	1/4"	BSPT Tapered	1.5mm		178-0964
St/Steel	1/4"	BSPT Tapered	3.0mm	70643733	381-7384
St/Steel	1/4"	BSPT Tapered	4.0mm	70643733	178-0965
St/Steel	1/4"	BSPT Tapered	4.5mm	70657796	839-9604
St/Steel	1/4"	BSPT Tapered	6.0mm	70643734	381-7390
St/Steel	1/4"	BSPT Tapered	1/4"	70657797	839-9608
St/Steel	1/4"	BSPT Tapered	1/8"	70657795	839-9601
St/Steel	1/4"	BSPT Tapered	3/16"	70657790	839-9585
St/Steel	1/2"	BSPT Tapered	3.0mm	70657777	839-9541
St/Steel	1/2"	BSPT Tapered	4.5mm	70637828	286-787
St/Steel	1/2"	BSPT Tapered	6.0mm	70637829	286-793
St/Steel	1/2"	BSPT Tapered	8.0mm	70657780	839-9550

Type	Thread Type	Pitch	Suits Probe Ø	Allied code	RS order code
St/Steel	M8	1mm	1.0mm		136-5856
St/Steel	M8	1mm	1.5mm		136-5857
St/Steel	M8	1mm	2.0mm		136-5858
St/Steel	M8	1mm	3.0mm		136-5859
St/Steel	M8	1mm	4.0mm		178-0966
St/Steel	M8	1mm	4.5mm		178-0967
St/Steel	M8	1mm	1/8"		178-0968
St/Steel	M8	1mm	3/16"		178-0969
St/Steel	M16	1.5mm	3.0mm	70657800	839-9617
St/Steel	M16	1.5mm	4.5mm		178-0970
St/Steel	M16	1.5mm	6.0mm	70657798	839-9610
St/Steel	M16	1.5mm	8.0mm	70657799	839-9614
St/Steel	M20	1.5mm	1.5mm		178-0971
St/Steel	M20	1.5mm	3.0mm		136-5860
St/Steel	M20	1.5mm	4.5mm		136-5861
St/Steel	M20	1.5mm	6.0mm		136-5862
St/Steel	M20	1.5mm	8.0mm		178-0972

Stainless Steel locknuts also available:

Thread	Allied code	RS order code
S/Steel 1/8" BSPP	70651759	762-1180
S/Steel 1/4" BSPP	70651760	762-1184
S/Steel 1/2" BSPP	70651762	762-1193

