

## FEATURES

- Big digit display
- Shock resistant
- Water resistant
- 3.0v lithium battery
- 70gm weight
- 1/100sec stopwatch for 40 minutes, then 1 sec to 23h, 59m, 59s.
- Time of day with calendar
- Daily alarm
- Hourly chime

## RS PRO Stopwatches

RS Stock No.: 241-3114



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

Big digit LCD stopwatch suitable for sports, industry, healthcare, science and any application where accurate time measurement is required.

- Water and shock resistant case
- Accuracy within 2 seconds a day
- 1/100 second count up to 40 minutes
- 1 second count up to 23h, 59m, 59s.
- Normal time with alarm
- Supplied with a cord lanyard

## General Specifications

<b>Type</b>	Pocket
<b>Digital/Analogue</b>	Digital
<b>Maximum Time</b>	23h 59min 59s;
<b>Resolution</b>	1; 0.01 s
<b>Maximum Time Hours</b>	23h
<b>Maximum Time Minutes</b>	59min
<b>Maximum Time Seconds</b>	59s
<b>Calibrated Service Type</b>	
<b>Countdown Timer</b>	No
<b>Accuracy</b>	2 second over 24 hours
<b>Functions</b>	Start/Stop/Reset
<b>Back Light</b>	No
<b>Alarm Function</b>	Yes
<b>Calendar</b>	Yes
<b>Water Resistance</b>	Water Resistant
<b>Case Material</b>	Plastic
<b>Colour/Finish</b>	Black
<b>Digit Heights</b>	12.4mm & 10.8mm
<b>Display</b>	LCD Single
<b>Memory</b>	No

## Electrical Specifications

<b>Operating Voltage</b>	1.5V;
<b>Battery Type</b>	CR2032 Lithium
<b>Battery Life</b>	Up to 5 years under normal use
<b>Solar Power</b>	No

## Mechanical Specifications

<b>Dimension</b>	77mm x 62.6mm x 24.6mm
<b>Depth</b>	24.6mm
<b>Height</b>	77mm
<b>Width</b>	62.6mm
<b>Weight</b>	70g

## Protection Category

<b>IP Rating</b>	IP 65
------------------	-------

## Classification

<b>eCl@ss Version</b>	None
<b>UNSPSC Version</b>	none

## Approvals

<b>Compliance/Certifications</b>	UKCA, CE, WEEE approved
<b>Declarations</b>	none

**Similar Products**

Parameters		Stock#
Brand	RS PRO	8111814
Type		Pocket/neck cord
Digital/Analogue		Digital
Maximum Time		23h, 59m, 59s
Resolution		1/100s; 1s
Maximum Time Hours		23
Maximum Time Minutes		59
Maximum Time Seconds		59
Countdown Timer		no
Accuracy		+/- 2 sec/day
Functions		s/w, time, calendar
Back Light		No
Alarm Function		yes
Calendar		Yes
Water Resistance		Yes
Operating Voltage		3 volt
Battery Type		CR2032 lithium
Battery Life		Up to 5 years
Solar Power		no
Digit Heights		12mm, 10mm
Display		LCD
Memory		no