


REV	DESCRIPTION	DATE
-----	-------------	------

NOTE :

1. MAXIMUM ELECTRIC CURRENT :

A.W.G.	16	14
AMP.	18	30
2. MAXIMUM ELECTRICAL RATING : 75°C 600 VOLTS MAX.
3. INSULATION MATERIAL : VINYL
4. INSULATION COLOR : BLUE
5. TERMINAL MATERIAL : COPPER
6. WIRE RANGE : 16-14 A.W.G. (1.5-2.5 mm²)
7. TERMINAL SURFACE TREATMENT : TIN PLATED
8. TERMINAL THICKNESS : 0.80 mm

Tolerance Unless Otherwise Specified	
0 > 6 mm ± 0.20	ANGLE
6 > 18 mm ± 0.30	0° ° REF ±
18 > 30 mm ± 0.40	° ° ±
30 > 75 mm ± 0.50	° ° ±

NAME	VINYL-INSULATED (MOLDED) SPADE TERMINALS			UNIT	mm	
PART NO.	SVYS2-4@	MATERIAL	-----	APPROVE		
NUMBER	KA-96125-C	SCALE	SHEET	PAGE	CHECKED	
DATE	2007/01/16	4/1	1-0	20F2	DRAWN	張 馨 尹