

FEATURES

- High Temperature cable tie, Max. operating temperature up to **150°C**
- UL approved Nylon 46, 94V-2
- One piece self-lock cable tie save the time
- Simple and quick to install

RS PRO Cable Ties

RS No.: 2243146



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- Material: UL approved Nylon 46, 94V-2.
- Color: Standard color is natural, other special colors are available upon request.
- Higher temperature cable tie, Max. operating temperature up to **150°C**
- Application: One piece self-lock cable tie save the time and make effective for installation.

General Specifications

| | |
|--------------------------------------|---|
| Series | Extra High temperature cable tie |
| Type | Non-Releasable |
| Colour | Natural |
| Material | Nylon 46, 94V2 |
| Finish | |
| Application | One piece self-lock cable tie save the time |
| Resistant To | |
| UV Resistant | No |
| Minimum Operating Temperature | |
| Maximum Operating Temperature | 150°C |
| Fire Behaviour | Self-Extinguishing |
| Quantity | 100 |

Mechanical Specifications

| | |
|----------------------------|----------------|
| Length | 300mm(11 7/8") |
| Width | 4.8mm |
| Tensile Strength | 22KGS(50lbs) |
| Maximum Bundle Dia. | 83mm |
| Thickness | 1.5±0.25mm |

Protection Category

IP Rating

Classification

eCl@ss (10.0.1)

UNSPSC (6.01)

Approvals

Declarations

Standards Met

RoHS, HF

Similar Products

| Stock No. | Brand | Product Name | Colour | Material | Tensile strength |
|-----------|--------|--------------|--------|----------|------------------|
| 206-6626 | RS PRO | | | NYLON46 | 18KGS(176.4N) |
| 206-6627 | RS PRO | | | NYLON46 | 22KG(215.6N) |
| 206-6628 | RS PRO | | | NYLON46 | 22KG(215.6N) |

