

特点

- dB 分辨率
- 60dB 动态范围
- 重量约 260 g
- 提供 30dB 至 130dB 测量
- 4 位 LCD 显示屏

RS PRO RS-95 声级计 8kHz

RS 库存号: 155-8902



RS 认证产品为您提供所有产品类别的专业品质部件。我们的产品系列经过工程师测试、提供与杰出品牌相当的质量、而无需支付高昂的价格。

介绍具有蓝牙功能的 RS PRO RS-95 声级计。由于其蓝牙功能，此高质量声级计可将声级数据轻松传输至用户的手机，以便分析数据。它是用于精确和高质量声音测量的极佳装置，具有 35 dB 至 130 dB 的动态范围。从 A 到 C 的频率加权有助于管理人耳的声级，即使在高分贝或高频环境中工作时也是如此。

一般规格

| | |
|--------|--------------------------|
| 型号 | RS-95 |
| 声级测量范围 | 35dB -130dB |
| 麦克风 | 1/2 英寸驻极体电容器麦克风 |
| 频率范围 | 31.5Hz-8KHz |
| 精确度 | 3dB (参考条件为 94dB , 1 kHz) |
| 频率 权重 | A , C |
| 显示类型 | LCD |

电气规格

| | |
|----|----------|
| 电源 | 一节 9V 电池 |
|----|----------|

机械规格

| | |
|----|---------------------|
| 尺寸 | 18mm x 54 毫米 x 36mm |
|----|---------------------|

操作环境规格

| | |
|---------|--------------|
| 工作湿度 | 10%RH-90%RH |
| 工作温度范围: | - 0°C 至 40°C |
| 存储温度范围 | -10°C 至 60°C |

认证

| | |
|----------|------|
| 合规性 / 认证 | rohs |
|----------|------|



6. Specifications

| | |
|-------------------------------------|--|
| Frequency range | 31.5Hz ~ 8KHz |
| Accuracy | 3dB (under reference condition of 94dB, 1 kHz) |
| Range | 35 ~ 130dB |
| Measuring range | LO: 35dB ~ 80dB Med: 50dB ~ 100dB HI: 80dB ~ 130dB Auto: 35dB ~ 130dB |
| Frequency weighting | A and C |
| Microphone | 1/2 inch electret condenser microphone |
| Digital display | 4 digits LCD display with a resolution: 0.1dB |
| Display Update | 2 times/sec |
| Auto power off | Meter automatically shuts down after approx. 10 minutes of inactivity |
| Power supply | One 9V battery |
| Low battery indication | The low battery signal "☹" flash when battery voltage drops below 7.2V; The backlight and low battery signal "☹" flash twice when battery voltage drops below 6.5V, then auto power off |
| Operation temperature and humidity | 0°C ~ 40°C, 10%RH ~ 90%RH |
| Storage temperature and temperature | -10°C ~ 60°C, 10%RH ~ 75%RH |
| Dimensions | 185 mm x 54 mm x 36 mm |

18/12/2017 Version No. 001

3