

Features

- This set from RS PRO is ideal for cleaning and repairing damaged or corroded threads
- The HSS construction of the pieces in the set allows for easy and clean cutting into metals, as well as durability and longer tool life
- This tools in this set offer a 3-stage tapping procedure (taper/starter, intermediate and bottoming)

RS PRO 32PCS HSS Tap and Die Set M3-M12

RS Stock No.: 2268889



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- RS PRO offers this high quality Tap and Die sets. Featuring all the essential pieces of equipment and accessories needed to successfully clean or cut new threads on fasteners, holes and much more. The HSS (High-Speed Steel) material makes it easier to cut harder materials with precision and efficiency, so this set is ideal for the professional craftsman or general engineering and automotive applications.*

General Specifications

Type:	Straight flute
Material	HSS
Set Contents	<ul style="list-style-type: none">- 21pcs DIN352 HSS Taps, 3pc each size: M3x0.5, M4x0.7, M5x0.8, M6x1.0, M8x1.25, M10x1.5, M12x1.75- 7pcs DIN 223 HSS Round Dies 25x9, without split: M3x0.5, M4x0.7, M5x0.8, M6x1.0, M8x1.25, M10x1.5, M12x1.75- 1pcs Tap Wrench: No.1 1/2- 1pcs Die Holder: 25x9mm- 1pc Pitch Gauge- 1pc Screwdriver- In metal box

