

Datasheet

RS Pro Insulated Crimp Spade Connector, 4mm² to 6mm², 12AWG to 10AWG, M4 Stud Size, Yellow Vinyl

RS Stock No: **613-9564**



Product Details

RS Pro insulated crimp spade connector in red vinyl colour, has 4 to 6 mm², 12 to 10 AWG wire size with M4 stud size. It is made from copper and tin plating. The spade terminal has vinyl or nylon insulation with flared design for easy wire insertion. The insulation of this electrical spade connector is colour coded to correspond with the wire size they are used with.

Features and Benefits

- Insulated crimp spade connectors made from copper with a tin plating
- Spade terminals is vinyl or nylon insulation with a flared design for easy wire insertion
- Insulation of these electrical spade connectors is colour coded to correspond with the wire size they are used with

Specifications:

Colour	Yellow
Contact Material	Copper
Contact Plating	Tin
Insulation	Insulated
Insulation Material	Vinyl
Maximum Wire Size (AWG)	10 AWG
Maximum Wire Size (mm ²)	6 mm ²
Minimum Wire Size (AWG)	12 AWG
Minimum Wire Size (mm ²)	4 mm ²
Overall Length	20.4 mm
Stud Size	M4.3
Thickness	1 mm
Width	7.2 mm
Wire Size	12 to 10 AWG
Current Rating	35 to 50 A
Temperature Rating	+105°C
Type	Butted Stem
Voltage Rating	600 V