


RoHS

REV	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2024.05.24



SPECIFICATIONS

- Current rating: 1A
- Temperature range: -40°C ~ +105°C
- Insulation resistance: 1000MΩ Min.
- Withstanding voltage: 500V AC/ minute.
- Contact resistance: 30mΩ Max.




Material:

Insulator Material:PA6T (UL 94V-0) Black
 Contact Material:Brass
 Plating:Matte Tin or gold plated over Nickel

Ordering Code:

BH127VS-XXP-H49
 1 2

- 序列号
- Pin位数: 2x03=06P



P.C.B Hole Layout

X.±0.50	X.°±
.X±0.25	.X°±
.XX±0.15	.XX°±
.XXX±0.10	.XXX°±
UNITS:	mm

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN

PART NO: BH127VS-XXP-H49		XFCN 兴飞连接器		
TITLE: 1.27mm Box Header Connectors		0769-82001899		
		www.xfconn.com		
		DWG NO:		
APPD	Chen ZhiQiang	VIEW		
CHKD	Liu Wei	SCALE	SHEET	REV
DRAW	Chen HongJiang	NONE	1/1	A1
DATE	2024.11.22			