





### SPECIFICATIONS

Current Rating: 3Amps  
 Insulation Resistance: 1000MΩ Min  
 Contact Resistance: 20mΩ Max  
 Withstanding Voltage: AC 1000V  
 Operation Temperature: -40° to +105°  
 Contact Material: Brass  
 Standard: PA6T  
 Insulator Material: Polyester(UL 94V-0)  
 Contact Plating: Gold Flash  
 Max.Processing Temp: 240°C for 30-60seconds  
 (260°C for 5seconds)

P/N	PIN	DIM.A	DIM.B
XY-2.54-1*01PZ	1	0.00	2.54
XY-2.54-1*02PZ	2	2.54	5.08
XY-2.54-1*03PZ	3	5.08	7.62
XY-2.54-1*04PZ	4	7.62	10.16
XY-2.54-1*05PZ	5	10.16	12.70
XY-2.54-1*06PZ	6	12.70	15.24
XY-2.54-1*07PZ	7	15.24	17.78
XY-2.54-1*08PZ	8	17.78	20.32
XY-2.54-1*09PZ	9	20.32	22.86
.....	.....	.....	.....
XY-2.54-1*40PZ	40	(PIN-1)X2.54	(PIN)X2.54



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: 2.54PH H2.5 1xnPin 180# PC3.0 PA6.0 PB2.5 L11.5 6T	
.X±0.3	X.*± 5°	CHK.	Jack	DWG NO. XY-2.54-1*NPZ	
.XX±0.2	.X*± 1°	DRA.	Can	CUSTOMER DRAWING	
.XXX±0.1	.XX*± 0.5°	SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A