



0010505


Jingweitang Industrial Zone,
Dalingshan Town, Dongguan City

Sales: Ms. Wang

Mobile number : +86 189-4861-7861

Web: [Http://www.yufengciye.com](http://www.yufengciye.com)

E-mail: yufengciye@126.com



Product Category	Core Marking			Coating Color
	Lot Number	Part Number	Inductance Grade	
Ferrite Core	2601	0010505	N/A	Green

Dimensions	Uncoated		Coated Limits			Packaging Box Qty=230 pcs
	(mm)	(in)	(mm)	(in)		
OD (A)	25.30	0.997	26.06	1.027	MAX	
ID (C)	14.93	0.588	14.18	0.559	MIN	
HT (B)	10.32	0.407	10.94	0.431	MAX	

Electrical Characteristics			Physical Characteristics						
IMPEDANCE RESULT (Testing Condition:0.65x0.5TSx120mm)			Initial Permeability	Saturation Magnetic Flux Density	Remanence	Coercivity	Density	Material	Weight (g)
@100Mhz	65Ω	50%							

The Limit of Breakage					Temperature Rating	
Winding Length Per Turn			Wound Coil Dimensions (mm)			Curie Temp: >160°C
Winding Factor	(mm)	Winding Factor	(mm)	40% Winding Factor		Coating Temp (Continuous up to): 180°C
				OD	HT	
-	-	-	-	Max OD	-	Notes:
-	-	-	-	Max HT	-	
Completely Full Window				Surface Area (mm ²)		
Unwound Core				-		
40% Winding Factor				-		

IMPEDANCE V.S FREQUENCY

