






REV.	Q'TY	ECN. NO.	APR.	DATE



Specifications:

Electrical:

- 1.Current Rating  
1.5A/contact terminal
- 2.Voltage Rating  
30V DC
- 3.Contact Resistance  
30 milliohms MAX
- 4.Dielectric Withstanding Voltage:  
500 V AC AT Sea Level
- 5.Insulation Resistance:  
1000MEGA ohms MIN

Mechanical:


- 1.Connector Mate and Unmate Force  
Mate force:3.75kgf (MAX)  
Unmate force:1.02kgf (MIN)
- 2.Terminal Retention:1.2kgf (MIN)

Material:

- 1.Housing:Hing Temperature Tnermaplastics,UL 94V-0  
PBT/LCP White/Black
- 2.Contact:Copper Alloy C2680
- 3.Shell: Copper Alloy C2680/SPCC

Finish:

- 1.Contact: Plated Gold in Mating Area;Tin On Solder Talls
- 2.Shell: Nickel Plating



PCB.WELDING DRAWING (TOLERANCE:±0.05)

Pin Definition		
PIN	Signal Name	Describe
1	VBUS	+5V
2	D-	Neagative Data Channel
3	D+	Positive Data Channel
4	GND	Ground

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyecomm Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: USB-AM-SMD-90°	
.X±0.3	X.*± 5°	CHK.	Jack	DWG NO. XY-USB-AM 180	
.XX±0.25	.X*± 1°	DRA.	Can	CUSTOMER DRAWING	
.XXX±0.15	.XX*±	SIZE	A4	SCALE	1:1
			SHEET	1/1	REV. A