






REV.	Q'TY	ECN. NO.	APR.	DATE




技术要求 Specification:

1. 材质 Material: PA66 UL94V-0;
2. 额定电流 Current rating: 3.0A AC, DC
3. 额定电压 Voltage rating: 250V AC, DC
4. 温度范围 Temperature range: -25°C to +85°C
5. 接触电阻 Contact resistance: ≤ 20mΩ
6. 绝缘电阻 Insulation resistance: > 1000MΩ
7. 耐压 Withstand voltage: 1000V AC/minute
8. 塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrs, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.



Part No	Pin	A	B	C	D
W-XHP-2-J	2	2.50	5.70	3.70	3.70
W-XHP-3-J	3	5.00	8.20	6.20	6.20
W-XHP-4-J	4	7.50	10.70	8.70	8.70
W-XHP-5-J	5	10.00	13.20	11.20	11.20
W-XHP-6-J	6	12.50	15.70	13.70	13.70
W-XHP-7-J	7	15.00	18.20	16.20	16.20
W-XHP-8-J	8	17.50	20.70	18.70	18.70
W-XHP-9-J	9	20.00	23.20	21.20	21.20
W-XHP-10-J	10	22.50	25.70	23.70	23.70
W-XHP-11-J	11	25.00	28.20	26.20	26.20
W-XHP-12-J	12	27.50	30.70	28.70	28.70
W-XHP-13-J	13	30.00	33.20	31.20	31.20
W-XHP-14-J	14	32.50	35.70	33.70	33.70
W-XHP-15-J	15	35.00	38.20	36.20	36.20
W-XHP-16-J	16	37.50	40.70	38.70	38.70



DIMENSION IN mm		APR. Alex		TITLE: XH2.5MM HOUSING	
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.3	.X*±1*	CHK. Jack	DWG NO. W-XHP-N-J		
.XX±0.2	.X*±		PROJ. CUSTOMER DRAWING		
.XXX±0.1	.XX*±	DRA. Can	SIZE A4	SCALE 1:1	SHEET 1/1
			REV. A		