





SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for 30-60seconds
(260°C for 5seconds)

P/N	PIN	DIM.A	DIM.B
X-2100-S01PZ	1	0.00	2.54
X-2100-S02PZ	2	2.54	5.08
X-2100-S03PZ	3	5.08	7.62
X-2100-S04PZ	4	7.62	10.16
X-2100-S05PZ	5	10.16	12.70
X-2100-S06PZ	6	12.70	15.24
X-2100-S07PZ	7	15.24	17.78
X-2100-S08PZ	8	17.78	20.32
X-2100-S09PZ	9	20.32	22.86
.....			
X-2100-S40PZ	40	(PIN-1)X2.54	(PIN)X2.54



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: 2.54PH H2.5 1xnPin 180# PC3.0 PA6.0 PB2.5 L11.5 6T	
.X±0.3	X.*± 5°	CHK.	Jack	DWG NO. X-2100-SNPZ	
.XX±0.2	.X.*± 1°	DRA.	Can	PROJ.  CUSTOMER DRAWING	
.XXX±0.1	.XX.*± 0.5°	SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A