


# RoHS

REV	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2024.05.24



### SPECIFICATIONS

1. Current rating: 1A
2. Temperature range: -40°C ~ +105°C
3. Insulation resistance: 1000MΩ Min.
4. Withstanding voltage: 600V AC/ minute.
5. Contact resistance: 20mΩ Max.

### Material:


Insulator Material:PA6T (UL 94V-0) Black  
 Contact Material:Copper Alloy  
 Plating:Matte Tin or gold plated over Nickel

### Ordering Code:


BH128VS-2xXX-H57-R  
 1                      2

1.序列号


2.Pin位数: 2x03-2x32




WITH POST



NO POST



No.of PIN/ROW	Dimension	
	A	B
2x03	2.54	6.81
2x04	3.81	8.08
2x05	5.08	9.35
2x06	6.35	10.62
2x07	7.62	11.89
2x08	8.89	13.16
2x09	10.16	14.43
2x10	11.43	15.70
2x11	12.70	16.97
2x13	15.24	19.51
2x15	17.78	22.05
2x17	20.32	24.59
2x19	22.86	27.13
2x20	24.13	28.40
2x25	30.48	34.75
2x30	36.83	41.10
2x32	39.37	43.64



P.C.B Hole Layout

X.±0.50	X.°±
.X±0.25	.X°±
.XX±0.15	.XX°±
.XXX±0.10	.XXX°±
UNITS:	mm

PART NO: BH128VS-2xXX-H57-R

TITLE: 1.27mm Box Header Connectors

APPD: Chen ZhiQiang

CHKD: Liu Wei

DRAW: Chen HongJiang

DATE: 2024.07.19

**XFCN** 兴飞连接器

0769-82001899  
 www.xfconn.com

DWG NO: /

VIEW:

SCALE: SHEET: REV:

NONE 1/1 A1

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN