





### SPECIFICATIONS

Current Rating: 3Amps  
 Insulation Resistance: 1000MΩ Min  
 Contact Resistance: 20mΩ Max  
 Withstanding Voltage: AC 1000V  
 Operation Temperature: -40° to +105°  
 Contact Material: Brass  
 Standard: PA6T  
 Insulator Material: Polyester(UL 94V-0)  
 Contact Plating: Gold Flash  
 Max.Processing Temp: 240°C for 30-60seconds  
 (260°C for 5seconds)

P/N	PIN	DIM.A	DIM.B
XY PZ2.54-1x1 ZD	1	0.00	2.54
XY PZ2.54-1x2 ZD	2	2.54	5.08
XY PZ2.54-1x3 ZD	3	5.08	7.62
XY PZ2.54-1x4 ZD	4	7.62	10.16
XY PZ2.54-1x5 ZD	5	10.16	12.70
XY PZ2.54-1x6 ZD	6	12.70	15.24
XY PZ2.54-1x7 ZD	7	15.24	17.78
XY PZ2.54-1x8 ZD	8	17.78	20.32
XY PZ2.54-1x9 ZD	9	20.32	22.86
.....	.....	.....	.....
XY PZ2.54-1x40 ZD	40	(PIN-1)X2.54	(PIN)X2.54



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd		
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: 2.54PH H2.5 1xnPin 180# PC3.0 PA6.0 PB2.5 L11.5 6T
.X±0.3	X.*± 5°	CHK.	Jack	DWG NO. XY PZ2.54-1xNP ZD
.XX±0.2	.X*± 1°	DRA.	Can	PROJ.  CUSTOMER DRAWING
.XXX±0.1	.XX*± 0.5°	SIZE	A4	SCALE 1:1 SHEET 1/1 REV. A