


RoHS

| REV | ECN NO. | DESCRIPTION | DESIGN | APPROVAL | DATE |
|-----|---------|-------------|--------|----------|------------|
| A1 | NEW | 更换图框 | | | 2024.05.24 |



SPECIFICATIONS

- Current rating: 1.5A
- Voltage Rating: 250V AC/DC
- Temperature range: -40°C ~ +105°C
- Insulation resistance: 800MΩ Min.
- Withstanding voltage: 400V AC/ minute.
- Contact resistance: 20mΩ Max.




Material:

Insulator Material: Nylon (UL 94V-0) Black
 Contact Material: Copper Alloy
 Plating: Matte Tin or gold plated over Nickel

Ordering Code:

BH200VS-2xXX

1. 序列号
2. Pin位数: 2x02P-2x32P



P.C.B Hole Layout

| | |
|-----------|--------|
| X.±0.50 | X.°± |
| .XX±0.25 | .XX°± |
| .XX±0.15 | .XX°± |
| .XXX±0.10 | .XXX°± |
| UNITS: | mm |

| | | | | |
|-------------------------------------|----------------|-------------------|-------|-----|
| PART NO: BH200VS-2xXX | | XFCN 兴飞连接器 | | |
| TITLE: 2.00mm Box Header Connectors | | 0769-82001899 | | |
| | | www.xfconn.com | | |
| | | DWG NO: / | | |
| APPD | Chen ZhiQiang | VIEW | | |
| CHKD | Liu Wei | SCALE | SHEET | REV |
| DRAW | Chen HongJiang | | | |
| DATE | 2024.08.21 | NONE | 1/1 | A1 |

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN