


Part No	Pin	A	B	C
XY-SM02B-GHS-WB	2	1.25	5.75	3.75
XY-SM03B-GHS-WB	3	2.50	7.00	5.00
XY-SM04B-GHS-WB	4	3.75	8.25	6.25
XY-SM05B-GHS-WB	5	5.00	9.50	7.50
XY-SM06B-GHS-WB	6	6.25	10.75	8.75
XY-SM07B-GHS-WB	7	7.50	12.00	10.00
XY-SM08B-GHS-WB	8	8.75	13.25	11.25
XY-SM09B-GHS-WB	9	10.00	14.50	12.50
XY-SM10B-GHS-WB	10	11.25	15.75	13.75
XY-SM11B-GHS-WB	11	12.50	17.00	15.00
XY-SM12B-GHS-WB	12	13.75	18.25	16.25
XY-SM13B-GHS-WB	13	15.00	19.50	17.50
XY-SM14B-GHS-WB	14	16.25	20.75	18.75
XY-SM15B-GHS-WB	15	17.50	22.00	20.00
XY-SM16B-GHS-WB	16	18.75	23.25	21.25



- NOTES:
- 1.BASE: LCP
 - 2.PIN: Brass
 - 3.Solder Tab: Brass
- SPECIFICATIONS:
- 1.Spacing: 1.25
 - 2.Voltage Rating: 125V AC DC
 - 3.Current Rating: 1A AC,DC
 - 4.Insulation Resistance: 100MΩ Min
 - 5.Contact Resistance: 20mΩ Max
 - 6.Withstanding voltage: 500V AC 1/Minute
 - 7.Temperatuer Range: -25℃ ~+ 85℃

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyecomm Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	TITLE: WAFER GH1.25 0000		
.X±0.2	X.*± 5*	Alex	DWG NO. XY-SMNB-GHS-WB		
.XX±0.1	.X*± 3*	Jack	PROJ. CUSTOMER DRAWING		
.XXX±0.05	.XX*± 1*	Can	SIZE A4	SCALE 1:1	SHEET 1/1 REV. A