


RoHS

REV	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2024.05.24



SPECIFICATIONS

- Current rating: 2A
- Temperature range: -40°C ~ +105°C
- Insulation resistance: 1000MΩ Min.
- Withstanding voltage: 500V AC/ minute.
- Contact resistance: 20mΩ Max.



Material:

Insulator Material: PA6T (UL 94V-0) Black
 Contact Material: Copper Alloy
 Plating: Matte Tin or gold plated over Nickel
 Mate with PM200 /I200 series


Ordering Code:

BH200V-xxP
 1 2

1. 序列号
2. Pin位数: 2x03=06P



No.of PIN/ROW	Dimension	
	A	B
2x03	4.00	13.50
2x04	6.00	15.50
2x05	8.00	17.50
2x06	10.00	19.50
2x07	12.00	21.50
2x08	14.00	23.50
2x09	16.00	25.50
2x10	18.00	27.50
2x11	20.00	29.50
2x12	22.00	31.50
2x13	24.00	33.50
2x15	28.00	37.50
2x17	32.00	41.50
2x20	38.00	47.50
2x22	42.00	51.50
2x25	48.00	57.50
2x34	66.00	75.50



P.C.B Hole Layout

X.±0.50	X.°±
.X±0.25	.X°±
.XX±0.15	.XX°±
.XXX±0.10	.XXX°±
UNITS:	mm

PART NO: BH200V-xxP

TITLE: 2.00mm 简易牛角 双排 DIP 180°

APPD: Chen ZhiQiang

CHKD: Liu Wei

DRAW: Chen HongJiang

DATE: 2024.08.21

XFCN 兴飞连接器

0769-82001899
 www.xfconn.com

DWG NO: /

VIEW:

SCALE: SHEET: 1/1 REV: A1

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN