





REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

General tolerances(mm)													D	
0 ~ 3	>3 ~ 6	>6 ~ 10	>10 ~ 18	>18 ~ 30	>30 ~ 50	>50 ~ 80	>80 ~ 120	>120 ~ 180	>180 ~ 250	>250 ~ 315	>315 ~ 400	>400 ~ 500		>500
±0.12	±0.18	±0.2 2	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50	±2°

Product model	PIN	A	B
C381128L-2POG36	2	7.62	3.81
C381128L-3POG36	3	11.43	7.62
C381128L-4POG36	4	15.24	11.43
C381128L-5POG36	5	19.05	15.24
C381128L-6POG36	6	23.46	19.05
C381128L-7POG36	7	26.67	22.86
.....	....	.....	....
C381128L-24POG36	24	Px3.81	(P-1)x3.81



UL Standard	B	C	D
Rated Voltage(V)/Current(A)	300/10	/	300/10
IEC Standard			
Overvoltage Category/Pollution Degree	III/3	III/2	II/2
Rated Voltage(V)/Current(A)	160/10	200/10	400/10
Rate Impulse Voltage(KV)	2.5	2.5	2.5
Torque Tightening(N·m/Lb.in)	M2.0/0.2		
Wire Range(rigid and flexible)(mm <sup>2</sup> /AWG)	26~16/1.0		
Pitch(mm)/Poles	3.81/N=02~24P		
Stripping length(mm)	5~6		
Operating temperature(°C)	-40~+105		
Conform to RoHS	Yes		



ITEM	NAME OF PART	MATERIAL	NOTES
4	Screw	Steel	M2/Zn plated
3	Cage	Copper Alloy	M3/Ni Plated
2	Housing	PA66	UL94V-0
1	Pin header	Copper alloy	Sn plated

深圳聚兴泰电子科技有限公司  
 Shenzhen Juxingtai Electronic Technology Co., Ltd

TOLERANCE		PART NO.	TITLE:
		C381128L-NPOG36	Socket-type terminal
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG
MATERILA	---	CHED: Olvia	SCALE SHEET N:A 1/1
FINISH	---	APPD: Ava	