





SPECIFICATIONS

Current Rating: 3Amps
 Insulation Resistance: 1000MΩ Min
 Contact Resistance: 20mΩ Max
 Withstanding Voltage: AC 1000V
 Operation Temperature: -40° to +105°
 Contact Material: Brass
 Standard: PA6T
 Insrlator Material: Polyester(UL 94V-0)
 Contact Plating: Gold Flash
 Max.Processing Temp: 240°C for 30-60seconds
 (260°C for 5seconds)

P/N	PIN	DIM.A	DIM.B
XY-MTP254-1X1	1	0.00	2.54
XY-MTP254-1X2	2	2.54	5.08
XY-MTP254-1X3	3	5.08	7.62
XY-MTP254-1X4	4	7.62	10.16
XY-MTP254-1X5	5	10.16	12.70
XY-MTP254-1X6	6	12.70	15.24
XY-MTP254-1X7	7	15.24	17.78
XY-MTP254-1X8	8	17.78	20.32
XY-MTP254-1X9	9	20.32	22.86
.....
XY-MTP254-1X40	40	(PIN-1)X2.54	(PIN)X2.54



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: 2.54PH H2.5 1xnPin 180# PC3.0 PA6.0 PB2.5 L11.5 6T	
.X±0.3	X.*± 5°	CHK.	Jack	DWG NO. XY-MTP254-1XN	
.XX±0.2	.X*± 1°	DRA.	Can	PROJ. CUSTOMER DRAWING	
.XXX±0.1	.XX*± 0.5°	SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A