




REV.	DATE	ECN NO.	MODIFICATION	APPROVER
AO	2021.05.24		NEW	Jason

ISPECIFICATIONS:  
 1.Current Rating: 5A AC,DC  
 2.Voltage Rating:250V AC,DC  
 3.Dielectric Withstanding : 1500V AC/minute  
 4.Insulator Resiatnce: 1000MΩ Min  
 5. Contact Reistansce: 20mΩ Max  
 6.Operating Temperature : -25°C~+85°C  
 Material:  
 1.Material: Nylon UL94V-0 Black  
 Major Dimension:▼  
 Lead free and ROHS compliant product



CKT	A	B
2*1		5.20
2*2	3.00	8.20
2*3	6.00	11.20
2*4	9.00	14.20
2*5	12.00	17.20
2*6	15.00	20.20
2*7	18.00	23.20
2*8	21.00	26.20
2*9	24.00	29.20
2*10	27.00	32.20
2*11	30.00	35.20
2*12	33.00	38.20

GENERAL TOLERANCE			UNITS mm	NAME(INTENDED USE)	<b>ATOM</b> ® 深圳市爱特姆科技有限公司 SHENZHEN ATOM TECHNOLOGY CO., LTD.	
SELECT	✓		MAT'L	Housing		
TOL.	1	2	3	PART NO.(INTENDED USE)	TITLE: Customer Drawing For HOUSING 3.0 2*XP	
ON.	X.XXX	±0.10	±0.15	±0.20	HO300**-04***	PA66 黑色 胶芯 公壳
	X.XX	±0.15	±0.20	±0.25	FINISH	DWG NO.:
	X.X	±0.20	±0.25	±0.30	Q'TY	ATOM-A07121
	X.	±0.25	±0.30	±0.50	APPD: Abel	CHKD: Tom
ANGLE	±2'				DR: XCF	SCALE 1:1
						SHEET 1/1
						REV. AO