

A

B

C






D

E

F




REV	DESCRIPTION	DESIGN	DATE
A			

SCALE:1/2



Specifications:

Poles: 02 to 12
 Contact resistance: $\leq 10\text{m}\Omega$
 Insulation resistance: $\geq 1000\text{M}\Omega$
 Rated voltage: 250V AC DC
 Rated current: 5.0A AC DC
 Withstand Voltage: 1000V AC/minute
 Temperature Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
 Material: PA66 UL94V-0, BLACK



PIN.	DIM A	DIM B
2pin	3.00	6.90
3pin	6.00	9.90
4pin	9.00	12.90
5pin	12.00	15.90
6pin	15.00	18.90
7pin	18.00	21.90
8pin	21.00	24.90
9pin	24.00	27.90
10pin	27.00	30.90
11pin	30.00	33.90
12pin	33.00	36.90

ORDER INFORMATION:

A3001Y-**-AZK-P	
PART No. _____	PACKAGING: P=PE
No.OF CIRCUITS: 02-12	PLASTIC MATERIAL: AZK=PA66

浙江创都电子科技有限公司

TITLE:

3.00mmPITCH Housing

PART NO.:

MX3.0-1x*Y

DWG NO.:

GENERAL TOLERANCE

X.	± 0.50	X.	$\pm 5^{\circ}$
X.X	± 0.30	X.X	$\pm 2^{\circ}$
X.XX	± 0.20	X.XX	$\pm 1^{\circ}$

UNITS:
mm

USE:

CUSTOMER

APPD:

CHKD:

DR:

SCALE

1 : 1

SHEET

1 / 1

A

B

C

D

E

F