








RoHS

REVISIONS		
REV.	ECN NO.	DESCRIPTION
A1	2022/06/07	NEW DESIGN



- NOTE:
MAIN SPECIFICATION:
- Rated current: 250V AC, 15A
额定电流: 250V AC, 15A
 - DIELECTRIC WITHSTAND VOLTAGE: 1500VAC
耐电压: 1500V MAX
 - TEMPERATURE RANGE: -30 °C ~ 80 °C
使用温度: -30 °C ~ 80 °C
 - CONTACT RESISTANCE: 30 MILLIONHM MAX
接触电阻: 30 MILLIONHM MAX
 - INSULATION RESISTANCE: 1000 MEGOHMS MIN.
绝缘阻抗: 1000 MEGOHMS MIN.
 - AFTER DURABILITY(5000CYCLES)
寿命 (5000次)



序号	料号	名称	材料	数量	镀层	备注
6	X3023A-51-10N8	螺钉	H59黄铜	2	Ni	
5	X3020-10-N3B	后盖	PA66 UL 94HB	1	BLACK	
4	X3023-42-21G6	插针 1+ 2+	QSn6.5-0.1 t=0.4	2	Ag	
3	X3023-41-21G6	插针 1- 2-	QSn6.5-0.1 t=0.4	2	Ag	
2	X3020-81-41C8	锁片	SPCC t=0.4	1	CuSn	
1	X3023A-00-N3B	底座	PA66 UL 94HB	1	BLACK	

X.±0.20	X.°±8°	Customer P/N:	浙江创都电子科技有限公司		
.X±0.15	.X°±5°	Customer REV.:			
.XX±0.07	.XX°±3°	PART NO.:	XLR-E05-LM4DJ-H-AG		
.XXX±0.05	.XXX°±1.5°	APPD:	DWG NO: XLR-E05-LM4DJ-H-AG		
UNITS: mm		CHKD:			
D TYPE	CUSTOMER D 客户图	DRAW:		SCALE	SHEET
			1:1	1/1	REV. A1