

A

B

C

D

E

F

REV	DESCRIPTION	DESIGN	DATE
A			

1

2

3

4

5

1




2

3





4

5

SCALE:1/2



LAST CIRCUIT

FIRST CIRCUIT
IDENTIFIER SYMBOL

Specifications:

Contact resistance: $\leq 10\text{m}\Omega$ Insulation resistance: $\geq 1000\text{M}\Omega$

Rated voltage: 250V AC DC

Rated current: 5.0A AC DC

Withstand Voltage: 1000V AC/minute

Temperature Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$

Housing: PA66 UL94V-0, BLACK

ORDER INFORMATION:

A3001Y-2**-A7K-P		
PART No.		PACKAGING: P=PE
No.OF CIRCUITS:		
201~212		
PLASTIC MATERIAL:		
A76K=PA66(BLACK)		

浙江创都电子科技有限公司

TITLE:

3.0mm PITCH Housing

GENERAL TOLERANCE

X. ± 0.50 X. $\pm 5^{\circ}$ X.X ± 0.30 X.X $\pm 2^{\circ}$ X.XX ± 0.20 X.XX $\pm 1^{\circ}$ UNITS:
mm

USE:

CUSTOMER

APPD:

CHKD:

DR:

PART NO.:

MX3.0-2×*Y

DWG NO.:

SCALE

1 : 1

SHEET

1 / 1

A

B

C

D

E

F