




RoHS

REVISIONS		
REV.	ECN NO.	DESCRIPTION
A1	2022/7/28	NEW DESIGN



Panel cut out






PCB layout(component-side)


NOTE:

MAIN SPECIFICATION:

- Rated current: 50V AC, 6A  
额定电流: 50V AC, 6A
- DIELECTRIC WITHSTAND VOLTAGE: 1000VAC  
耐电压: 1000V MAX
- TEMPERATURE RANGE: -30 °C ~ 80 °C  
使用温度: -30 °C ~ 80 °C
- CONTACT RESISTANCE: 30 MILLIONHM MAX  
接触电阻: 30 MILLIONHM MAX
- INSULATION RESISTANCE: 1500 MEGOHMS MIN.  
绝缘阻抗: 1500 MEGOHMS MIN.
- AFTER DURABILITY(1000CYCLES)  
寿命 (1000次)



Minimum installation spacing



序号	料号	名称	材料	数量	镀层	备注
4	X3014W-31-21S8	接地片(G#)	QSn6.5-0.1Y t=0.5	1	镀锡(Sn)	
3	X3015-42-10A1	短圆针(3#)	HPb59-1	1	镀金(Au)	
2	X3015-41-10A1	长圆针(1#2#)	HPb59-1	2	镀金(Au)	
1	X3014-00-N3B	底座(BASE)	PA66 UL 94HB	1	黑色(BALCK)	

X.± 0.20	X.°±8°
.X± 0.15	.X°±5°
.XX± 0.07	.XX°±3°
.XXX±0.05	.XXX°±1.5°
UNITS:	mm
D TYPE	CUSTOMER D 客户图

Customer P/N:	
Customer REV.:	
PART NO.:	XLR-09W-NK-JD-H
APPD:	
CHKD:	
DRAW:	

浙江创都电子科技有限公司			
TITLE: XLR ,3孔卧式插座			
DWG NO: XLR-09W-NK-JD-H			
	SCALE	SHEET	REV.
	1:1	1/1	A1