





A
B
C
D
E
F
G



技术参数 (SPECIFICATION):

- 温度范围 (TEMPERATURE RANGE): -40~+70°C
- 额定电压 (VOLTAGE RATING): 125V
- 额定电流 (CURRENT RATING): 1.5A
- 接触电阻 (CONTACT RESISTANCE): ≤30mΩ
- 绝缘电阻 (INSULATION RESISTANCE): ≥500MΩ
- 耐压 (DIELECTRIC STRENGTH): 1000V AC/(50HZ)/Min
- 插拔力 (MATING AND UNMATING FORCE): 3~20N
- 寿命 (DURABILITY): 750 CYCLES MIN

材料 (MATERIAL):

- 塑座 (HOUSING): NYLON UL94V-0
- 插针 (CONTACT): PHOSPHOR BRONZE ø0.46mm
- 镀层 (PLATING): GOLD PLATING OVER NICKEL
- 外壳 (SHIELD): COPPER ALLOY PLATED NICKEL t=0.2mm

改
涂
意
随
上
面
图
在
止
禁

网络插座外形图

浙江创都电子科技有限公司

绘图:	日期:	14.03.01
审核:	日期:	
核准:	日期:	

料号:		RJ45-SP32CB-YGWT-H	
型号:		RJ45	
图号:			
单位:	mm	比例:	1:1
纸张:	A4		

版次	A/0	新出版发行
变更履历	1	2
变更单号	3	

变更单号	绘制	日期
------	----	----