



REVISIONS			
REV.	ECN NO.	DESCRIPTION	DATE
A1		\	2023.11.30

NOTE:  
MAIN SPECIFICATION:

- Rated current: 50V AC, 6A  
额定电流: 50V AC, 6A
- DIELECTRIC WITHSTAND VOLTAGE: 500VAC  
耐电压: 500V MAX
- TEMPERATURE RANGE: -30 °C ~ 80 °C  
使用温度: -30 °C ~ 80 °C
- CONTACT RESISTANCE: 30 MILLIONHM MAX  
接触电阻: 30 MILLIONHM MAX (AFTER TEST 50mΩ Max)
- INSULATION RESISTANCE: 1000 MEGOHMS MIN.  
绝缘阻抗: 1000 MEGOHMS MIN.
- AFTER DURABILITY(1000CYCLES)  
寿命 (1000次)

IM NO.	ASSY P/N	ITEM	PART P/N	QTY	NAME	NOTE
1		7	X3016-31-61N8	1PCS	弹片	65Mn, 整个底层镀镍
		6	X3016-81-61N8	1PCS	按柄	65Mn, 整个底层镀镍
		5	X532WP-46-11S8	1PCS	接地针	COPPER ALLOY, 镀锡
		4	X336WP-43-11A1	1PCS	3#端子	COPPER ALLOY, 镀金
		3	X336WP-42-11A1	1PCS	2#端子	
		2	X336WP-41-11A1	1PCS	1#端子	
		1	X336WP-01A-N3B	1PCS	底座	无logo, 黑色PA66

X.± 0.25	X.°±
.X± 0.20	.X°±5°
.XX± 0.15	.XX°±3°
.XXX±0.08	.XXX°±
UNITS:	mm

Customer P/N: \	浙江创都电子科技有限公司
Customer REV.: \	
PART NO.:	TITLE: 3芯母座90度, 独立接地:
APPD: 2023.11.30	XLR-08W-PJD-JH
CHKD: 2023.11.30	
DRAW:	SCALE SHEET REV. 1:1 1/1 A1

