




SCHEMATIC



技术特性:

- 使用条件: $-30 \sim 70^{\circ}$
- 额定负荷: DC 30V 0.5A
- 接触电阻: $\leq 0.03\Omega$
- 绝缘电阻: $\geq 100m\Omega$
- 耐压: AC500V (50Hz) /min
- 插拔力: 3~20N
- 寿命: 5000次

PCB LAYOUT
TOP VIEW (TOLERANCE: ± 0.05)



基座	PBT	1	
盖片	黄铜	1	AU
插脚 I	磷铜	1	AU
插脚 II	磷铜	2	AU
零件名称	材料	数量	

GENERAL TOLERANCES		
0.X	± 0.30	X° $\pm 3^{\circ}$
0.XX	± 0.20	
0.XXX	± 0.10	X.X° $\pm 1^{\circ}$
UNIT	SIZE	SCALE
MM	A4	1:1

DRAWN		C	TITLE: 耳机插座
DESIGN		PART NO.	PJ-322-AU
CHECKED		PRODUCT NO.	
APPROVED		DRAWING NO.	
		UNIT: mm	SCALE: 1:1 REV: 01-1 SHT: 10F 1

浙江创都电子科技有限公司

ECN NO.	REV	DATE	DESCRIPTION	MDF'D	APP'D
	01	2021.12.22	NEW DRAWING RELEASE		