




RoHS

REVISIONS		
REV.	ECN NO.	DESCRIPTION
A1	2022/06/07	NEW DESIGN







Panel cut out



PCB layout

NOTE:  
MAIN SPECIFICATION:

- Rated current: 250V AC, 15A  
额定电流: 250V AC, 15A
- DIELECTRIC WITHSTAND VOLTAGE: 1500VAC  
耐电压: 1500V MAX
- TEMPERATURE RANGE: -30 °C ~ 80 °C  
使用温度: -30 °C ~ 80 °C
- CONTACT RESISTANCE: 30 MILLIONHM MAX  
接触电阻: 30 MILLIONHM MAX
- INSULATION RESISTANCE: 1000 MEGOHMS MIN.  
绝缘阻抗: 1000 MEGOHMS MIN.
- AFTER DURABILITY(5000CYCLES)  
寿命 (5000次)



序号	料号	名称	材料	数量	镀层	备注
6	X3020W-10-N3B	后盖	PA66 UL 94HB	1	黑色	
5	X3020W-43-21G6	插针 2+	QSn6.5-0.1 t=0.4	1	Ag	
4	X3020W-42-21G6	插针 1+	QSn6.5-0.1 t=0.4	1	Ag	
3	X3020W-41-21G6	插针 1- 2-	QSn6.5-0.1 t=0.4	2	Ag	
2	X3020-81-41C8	锁片	SPCC t=0.4	1	CuSn	
1	X3023F-00-N3B	底座	PA66 UL 94HB	1	黑色	

X.±0.20	X.°±8°	Customer P/N:	浙江创都电子科技有限公司
.X±0.15	.X°±5°		
.XX±0.07	.XX°±3°	Customer REV.:	
.XXX±0.05	.XXX°±1.5°	PART NO.:	XLR-E07-WJ-WDH-AG
UNITS:	mm	APPD:	
		CHKD:	
		DRAW:	
D TYPE	CUSTOMER D		
	客户图		

TITLE:			Speakon,4pin立式四方座		
DWG NO.:			XLR-E07-WJ-WDH-AG		
SCALE	SHEET	REV.			
1:1	1/1	A1			

