





3P



2P



P.C.B LAYOUT

Ordering Information:

C4140WV-XP - ** - **
1 2 3

1.Part NO.

2.Material:

(Blank): Nylon 66,UL94V-0(White)

46:Nylon 46,UL94V-0(White)

GWT: Nylon 66,UL94V-0(Beige),IEC 60335-1,5th Edition
Glow Wire Capable.

3.Finish:

(Blank):Tin over Nickel

G:Gold over Nickel(1u")

G15:Gold over Nickel(15u")

G30:Gold over Nickel(30u")

SPECIFICATIONS:

Current Rating: 9A AC,DC

Voltage Rating: 600V AC,DC

Temperature Range: -40°C ~ +105°C

Contact Resistance: 20mΩ Max

Insulation Resistance: 1000MΩ Min

Withstanding Voltage: 1500V AC/minute

Pin Material: Brass

Ordering Information & Dimensions

Circuits	Dimensions(mm)			Circuits	Dimensions(mm)		
	A	B	C		A	B	C
2P	4.14	9.83	13.68	3P	8.28	13.97	17.82

CJTconn CHANGJIANG CONNECTORS CO.,LTD.

Unit	Scale	Sheet	TITLE
mm	3:1	1 of 1	4.14mm PITCH Vertical WAFER
DRAWN	CHK'D	APPR	
Xiaoyan Luo	Dlankul Wan	Jack Yin	
General Tolerances		THIRD ANGLE PROJECTION	DRAWING NO.
x.xx±0.25			C4140WV-XP
x.xxx±0.20			
x.xxxx±0.15			REV
ANGLES ±1°			A3

REV	DESCRIPTION	DATE
A3	JL-GC-ECN00284	2024.06.05
A2	CHANGE THE DRAWING	2023.09.05
A1	CHANGE THE DRAWING	2021.08.26
A0	NEW RELEASE	2015.04.13