



REVISIONS			
REV.	ECN NO.	DESCRIPTION	DATE
A1		\	2023.11.30

NOTE:
MAIN SPECIFICATION:

- Rated current: 50V AC, 6A
额定电流: 50V AC, 6A
- DIELECTRIC WITHSTAND VOLTAGE: 500VAC
耐电压: 500V MAX
- TEMPERATURE RANGE: -30 °C ~ 80 °C
使用温度: -30 °C ~ 80 °C
- CONTACT RESISTANCE: 30 MILLIONHM MAX
接触电阻: 30 MILLIONHM MAX (AFTER TEST 50mΩ Max)
- INSULATION RESISTANCE: 1000 MEGOHMS MIN.
绝缘阻抗: 1000 MEGOHMS MIN.
- AFTER DURABILITY(1000CYCLES)
寿命 (1000次)

X.± 0.25	X.°±	Customer P/N: \	浙江创都电子科技有限公司		
.X± 0.20	.X°±5°	Customer REV.: \	TITLE:		
.XX± 0.15	.XX°±3°	PART NO.:	3芯母座180度, 无LOGO, 锰钢按柄无接地		
.XXX±0.08	.XXX°±	APPD:	DWG NO:		
UNITS: mm		CHKD:	XLR-08ZJ-NJ-P-H		
		DRAW:	SCALE	SHEET	REV.
			1:1	1/1	A1

IM NO.	ASSY P/N	ITEM	PART P/N	QTY	NAME	NOTE
1		6	X3016-31-61N8	1PCS	弹片	65Mn, 整个底层镀镍
		5	X3016-81-61N8	1PCS	按柄	65Mn, 整个底层镀镍
		4	X337LP-43-11A1	1PCS	3#端子	COPPER ALLOY, 镀金
		3	X313-0402+A	1PCS	2#端子	
		2	X337LP-41-11A1	1PCS	1#端子	
				1	X336WP-01A-N3B	1PCS