



电路图



PCB. 焊接图

主要技术规格:

1. 额定值: 50mA DC12V
2. 接触电阻: $\leq 50m\Omega$
3. 操作力: $250 \pm 40gf$
4. 行程: $0.20 \pm 0.1mm$
5. 绝缘电阻: $\geq 100M\Omega$
6. 抗电强度: 250V 50HZ 1Min.
7. 寿命: 50,000 Cycles

										第一视角		名称: 轻触开关									
5	引脚、触点	黄铜	1	镀银								型号: TS-1101CC4PLH-3x6x**-**									
4	基座	PPA	1	耐温280℃ (黑色)								<table border="1"> <tr> <th colspan="2">一般公差</th> </tr> <tr> <td>>0.5~2</td> <td>±0.10</td> </tr> <tr> <td>>2~5</td> <td>±0.25</td> </tr> <tr> <td>>5~10</td> <td>±0.30</td> </tr> <tr> <td>角度</td> <td>±0.5°</td> </tr> </table>		一般公差		>0.5~2	±0.10	>2~5	±0.25	>5~10	±0.30
一般公差																					
>0.5~2	±0.10																				
>2~5	±0.25																				
>5~10	±0.30																				
角度	±0.5°																				
3	簧片	不锈钢	1	覆银	标记	处数	更改文件号	签名	日期	比例			浙江创都电子科技有限公司								
2	盖板	黄铜	1	镀锡	设计				单位	mm											
1	按钮	PPA	1	耐温280℃ (黑色)	审核				重量												
序号	零件名称	材料规格	数量	备注	批准																